

79 02 125 ESD


Precision Electronics Side Cutter ESD



- precision pliers for ultra fine cutting work, e. g. in electronics and fine mechanics
- very precisely ground and sharp cutting edges with very small bevels for exact cutting on delicate electronic components; also available without bevel for flush cutting
- electrically discharging handles - dissipative
- cutting edges additionally induction hardened, cutting edge hardness approx. 64 HRC
- approx. 20 % lighter than conventional electronics pliers
- bolted joint with particularly carefully manufactured joint surfaces for even, low-friction movement throughout the entire opening range
- smooth-running double spring for a gentle and even opening
- ergonomically optimised multi- component handles
- forged from chrome vanadium ball-bearing steel
- round head

The subtle difference

KNIPEX precision electronics pliers are made of high-quality ball bearing steel and processed with the highest degree of care. Each opening movement is gentle and even without backlash. Each work step proceeds reliably and precisely. This makes work much easier for professionals.




ESD pliers (electrostatic discharge)

electrostatic energy is discharged through the handles in a gradual and controlled manner

which protects components endangered by electrostatic discharge

in accordance with applicable standards, e.g. IEC TR 61 340-5, DIN EN 61 340-5, SP Method 2472

Article No.	79 02 125 ESD
EAN	4003773061519
Pliers	burnished
Head	polished
Handles	with multi-component grips
Style	0
medium hard wire Ø mm	1,3
hard wire Ø mm	0,7
soft wire Ø mm	0,2 - 1,7
B mm	10
D mm	6,5
A mm	11
Nominal size	125 mm
Length mm	125
Net weight g	61



technical change and errors excepted

