

300 Universal Beam Clamp

3000050PL



Features

- Conforms with Federal Specification WW-H-171 (Type 23), Manufacturers Standardization Society ANSI/MSS-SP-58 (Type 19 and 23), install in accordance with ANSI/MSS-SP-69

Product Specifications

Part Number	3000050PL
Material	Steel
Finish	Plain
Rod Size (RS)	1/2"
Flange Thickness (FT)	13/16" Max
A	1 1/8"
Screw Diameter (Sc)	7/16"
Torque (TQ)	8 ft lb
Static Load 1 (F1)	950 lb
Static Load 2 (F2)	760 lb
Standard Packaging Quantity	50 pc
UPC	78285634899
UNSPSC	31162905
Approvals	cULus®, FM®

Setscrew must be tightened and torqued onto the sloped side of the I-beam.

Recognizing that torque wrenches are generally not used or available on many job sites, the setscrew should be tightened so it contacts the I-beam and then an additional 1/4 to 1/2 turn added.

