

Dayton Utility Pumps

PUMPS technical data sheet



Submersible Utility / Dewatering pumps are designed for fluid transfer or dewatering applications. These pumps are typically used for temporary rain water removal and are designed to operate continuously. Utility pumps typically do not have automatic float switches, but do have broader head and flow ranges to accommodate higher performance requirements of dewatering applications.





3YU54 1/6 HP, Thermoplastic Submersible Utility Pump

HP	1/6
Voltage	115V
Phase	Single
Frequency	60 Hz
Run Amps	1.5A
RPM	3450
Motor Type	PSC – Oil Free

Overload Protection	Internal Thermal Overload
Motor Shaft Material	Stainless Steel
Motor Housing Material	Thermoplastic
Motor Duty	Intermittent
Motor End Bearing	Single Row Ball
Pump End Bearing	Single Row Ball
Lubrication	Permanently Lubricated
Discharge	1-1/4 Inch MNPT, Vertical
Volute Material	Thermoplastic
Base Material	Thermoplastic
Impeller Type	Open Vortex
Impeller Material	Thermoplastic
Hardware Material	Stainless Steel
O-rings	Buna-N
Seal Type	Single Mechanical
Seal Materials	Carbon/Ceramic/Buna-N
Operation	Manual Operation
Power Cord	18/3 SJTOW, 10' (3m), NEMA 5-15P 120V Plug
Max. Solids Handling	1/8" (3.2mm) spherical
Max. Water Temperature	140°F (60°C)
Designed Fluid Environment	Water / Wastewater


Outline Dimensions



Performance Data

Head	Feet	5	10	15	20
	Meters	1.5	3.1	4.6	6.1
Flow Rate	GPM	16	11	6	0
	LPM	61	42	23	0

Performance Chart



WARNING: Use only with nonflammable liquids compatible with pump component materials and in nonflammable/non-explosive atmospheres.

Find it at Grainger.

© 2013 W.W. Grainger, Inc.

Call or visit your local branch or go to grainger.com/dayton for complete product line information

