

Dayton Sewage Pumps

PUMPS technical data sheet



Submersible Sewage pumps are designed to remove sewage wastewater from a residential home or commercial office. These pumps are designed to pass the typical suspended solids associated with sewage wastewater. Sewage pumps typically operate intermittently and automatically with a float switch and can accommodate solids up to 2" in diameter.





4LE16 1½ HP, Cast Iron Submersible Sewage Pump

HP	1-1/2
Voltage	240V
Phase	Single
Frequency	60 Hz
Run Amps	16A
Start Amps	44.6A
RPM	1750
Motor Type	PSC Oil-filled with Class B insulation

Overload Protection	Internal Thermal Overload
Motor Shaft Material	Stainless Steel
Motor Housing Material	Cast Iron
Motor Duty	Continuous
Motor End Bearing	Single Row Ball
Pump End Bearing	Single Row Ball
Lubrication	Oil Lubricated
Discharge	3 Inch FNPT, Vertical
Volute Material	Cast Iron
Base Material	Cast Iron
Impeller Type	Open Vortex
Impeller Material	Cast Iron
Hardwear Material	Stainless Steel
O-rings	Buna-N
Seal Type	Single Mechanical
Seal Materials	Silicon Carbide/Silicon Carbide/Buna N
Operation	Manual Operation
Power Cord	12/3 SJOOW, 25' (7.6m), NEMA 6-15P 240V Plug
Max. Solids Handling	2-1/2" (64mm) spherical
Max. Water Temperature	104°F (40°C)
Designed Fluid Environment	Water / Sewage Wastewater


Outline Dimensions



Performance Data

Head	Feet	5	10	15	20	25	30	35	39
	Meters	1.5	3.1	4.6	6.1	7.6	9.1	10.7	11.9
Flow Rate	GPM	370	335	295	240	185	125	52	0
	LPM	1401	1268	1117	908	700	473	197	0

Performance Chart



WARNING: Use only with nonflammable liquids compatible with pump component materials and in nonflammable/nonexplosive atmospheres.

Call or visit your local branch or go to grainger.com/dayton for complete product line information

Find it at Grainger.

© 2013 W.W. Grainger, Inc.

