

i tape with



HOT MELT CARTON SEALING TAPES


WITH CORRU-GRIP™ ADHESIVE TECHNOLOGY

IPG® ANNOUNCES AN EXPANDED CORRU-GRIP™ PORTFOLIO!

According to recent studies, more than 90% of boxes contain recycled content. Changes in the fiber and composition of your cartons may impact the ability of your tape to adhere to it. IPG® has expanded its line of Hot Melt Carton Sealing Tapes that feature Corru-Grip™ Adhesive Technology to include **9100** and **8100** as well as 1100. All are designed to stick to every carton - especially recycled corrugate.

- Ground-breaking adhesive formulation, developed specifically for optimal closure of high percent content recycled corrugate
- Expanded application temperature and humidity range, unique for a Hot Melt product, provides superior closure
 - Down to 35°F and 25% relative humidity
 - At room temperature, 72°F and 50% relative humidity
 - At 105°F and 75% relative humidity
 - Ultimately up to 120°F
- Confidently and successfully seals boxes in more environmental conditions than any other product in its class
- Manufactured entirely and exclusively in the USA - your guarantee of quality and consistency

FEATURES & BENEFITS



Carton sealing tapes with IPG®'s

RECYCLED CORRUGATE FRIENDLY



ARE PROVEN

to pull more corrugate fibers than other products in its class.



Intertape™ Brand

Other Brand

SCAN

the QR code to view the Corru-Grip™ Test Video!



NOMINAL VALUES

STYLE	TOTAL THICKNESS	BACKING	ADHESIVE	ADHESION TO STEEL	TENSILE STRENGTH	SHEAR TO LINERBOARD ½" x ½" x 1000 grams	ELONGATION % at break	COLORS
	<i>ASTM D-3652</i>			<i>ASTM D-3330</i>	<i>ASTM D-3759</i>	<i>ASTM D-3654</i>	<i>ASTM D-3759</i>	
1100	3.0 mil (0.076mm)	2.0 mil (0.05 mm) Cast Film	Synthetic Rubber/Resin	46 oz/in of width (50.3 N/100mm)	32 lb/in of width (560 N/100mm)	10,000+ minutes	150%	Clear, Tan
9100	2.5 mil (0.064mm)	1.6 mil (0.041 mm) Cast Film	Synthetic Rubber/Resin	44 oz/in of width (48.2 N/100mm)	31 lb/in of width (543 N/100mm)	10,000+ minutes	120%	Clear, Tan
8100	2.2 mil (0.056mm)	1.4 mil (0.36 mm) Cast Film	Synthetic Rubber/Resin	42 oz/in of width (46.0 N/100mm)	23 lb/in of width (403 N/100mm)	10,000+ minutes	120%	Clear, Tan

1100 3 MIL PREMIUM

PRODUCT NO.	WIDTH (mm)	LENGTH (M)	COLOR	ROLLS/CASE	CASES/PALLET
F4210	48	55	Clear	36	60
F5210	48	55	Tan	36	60
F4225	72	55	Clear	24	60
F5225	72	55	Tan	24	60
F4139	48	100	Clear	36	48
F4066	72	100	Clear	24	60
F4220	48	914	Clear	6	36
F4240	72	914	Clear	4	36

9100 2.5 MIL PREMIUM

PRODUCT NO.	WIDTH (mm)	LENGTH (M)	COLOR	ROLLS/CASE	CASES/PALLET
F4185	48	55	Clear	36	60
F5185	48	55	Tan	36	60
F4200	72	55	Clear	24	60
F5200	72	55	Tan	24	60
F1192	48	100	Clear	36	48
F4202	72	100	Clear	24	48
F4195	48	914	Clear	6	48
F4208	72	914	Clear	4	48
F5205	72	914	Tan	4	48

8100 2.2 MIL MEDIUM

PRODUCT NO.	WIDTH (mm)	LENGTH (M)	COLOR	ROLLS/CASE	CASES/PALLET
F4140	48	50	Clear	36	72
F4150	48	100	Clear	36	48
F4166	72	100	Clear	24	48
F4155	48	914	Clear	6	48
F4160	48	1371	Clear	6	36
F4170	72	914	Clear	4	48
F4171	72	1371	Clear	4	36

ipg tape with



800-IPG-8273 / 800-474-8273

www.itape.com | E-mail: info@itape.com

©2013 Intertape Polymer Group® • CORRUGRIP™ EXPANSION SS • 031413 • Printed in the U.S.A.

