



intertape polymer group®

INDUSTRIAL PRODUCTS
CORE CATALOG



Surrounding Customers with Solutions!

As one of the most comprehensive suppliers of industrial and packaging products, Intertape Polymer Group (IPG) is uniquely positioned to touch a broad base of customers with specialized solutions. The product solutions engineered by Intertape are designed to create efficiencies, cost containment and performance advantages for the end use markets and applications served by IPG products. The Core Products highlighted in this catalog meet the needs of most widespread industrial applications. To learn more about the complete line of IPG products that range from general to highly specialized, log on to www.itape.com.



PAPER MASKING TAPE

Intertape® brand Paper Masking Tapes are designed for superior performance in a variety of applications and environments ranging from demanding temperature and UV sensitive paint masking to general purpose functions such as holding or light duty splicing, bundling and more.



UV RESISTANT

PT14 UV Resistant 14-Day Blue Masking Tape



- Removes cleanly up to 14 days after application, even when exposed to direct sunlight and high humidity
- Fine crepe paper backing

Item Number	Size	Tensile lb/in	Adhesion oz/in	Thickness mils	Elongation %	Color	Rolls/Case
PT14..35	18mm x 54.8m	23	26	5.5	11	Blue	48
PT14..36	24mm x 54.8m	23	26	5.5	11	Blue	36
PT14..37	36mm x 54.8m	23	26	5.5	11	Blue	24
PT14..38	48mm x 54.8m	23	26	5.5	11	Blue	24

PT8 UV Resistant 8-Day Green Masking Tape



- Removes cleanly up to 8 days after application, even when exposed to direct sunlight and high humidity
- Fine crepe paper backing

Item Number	Size	Tensile lb/in	Adhesion oz/in	Thickness mils	Elongation %	Color	Rolls/Case
85283	18mm x 54.8m	18	22	5.9	11	Green	48
85284	24mm x 54.8m	18	22	5.9	11	Green	36
85285	36mm x 54.8m	18	22	5.9	11	Green	24
85286	48mm x 54.8m	18	22	5.9	11	Green	24

PREMIUM GRADE

PG5 Premium Grade Masking Tape



- Smooth textured backing
- Easy application
- Clean, crisp paint lines

Item Number	Size	Tensile lb/in	Adhesion oz/in	Thickness mils	Elongation %	Color	Rolls/Case
PG5...127	18mm x 54.8m	25	30	6.3	10	Natural	48
PG5...128	24mm x 54.8m	25	30	6.3	10	Natural	36
PG5...129	36mm x 54.8m	25	30	6.3	10	Natural	24
PG5...130	48mm x 54.8m	25	30	6.3	10	Natural	24

MEDIUM GRADE

519 Medium Grade Masking Tape



- Solvent cast natural and synthetic rubber blend adhesive
- Adheres to many surfaces

Item Number	Size	Tensile lb/in	Adhesion oz/in	Thickness mils	Elongation %	Color	Rolls/Case
73848	18mm x 54.8m	23	36	6.0	7	Natural	48
73858	24mm x 54.8m	23	36	6.0	7	Natural	36
73859	36mm x 54.8m	23	36	6.0	7	Natural	24
73860	48mm x 54.8m	23	36	6.0	7	Natural	24

UTILITY GRADE

PG505 Utility Grade Masking Tape



- Paint contractor industry staple
- High elongation will conform to most painting applications

Item Number	Size	Tensile lb/in	Adhesion oz/in	Thickness mils	Elongation %	Color	Rolls/Case
PG505.120	18mm x 54.8m	20	30	5.8	10	Natural	48
PG505.121	24mm x 54.8m	20	30	5.8	10	Natural	36
PG505.122	36mm x 54.8m	20	30	5.8	10	Natural	24
PG505.123	48mm x 54.8m	20	30	5.8	10	Natural	24

515 Utility Grade Masking Tape



- Proven industry leader
- Solvent cast natural and synthetic rubber blend adhesive
- Ideal for masking, bundling and holding

Item Number	Size	Tensile lb/in	Adhesion oz/in	Thickness mils	Elongation %	Color	Rolls/Case
70830	18mm x 54.8m	21	40	6	7	Natural	48
70885	24mm x 54.8m	21	40	6	7	Natural	36
70934	36mm x 54.8m	21	40	6	7	Natural	24
70988	48mm x 54.8m	21	40	6	7	Natural	24

PG415 Utility Grade Masking Tape



- Very conformable backing and aggressive adhesive
- For non-critical securing and bundling applications

Item Number	Size	Tensile lb/in	Adhesion oz/in	Thickness mils	Elongation %	Color	Rolls/Case
85328	18mm x 54.8m	20	37	5.3	8	Natural	48
85324	24mm x 54.8m	20	37	5.3	8	Natural	36
85325	36mm x 54.8m	20	37	5.3	8	Natural	24
85326	48mm x 54.8m	20	37	5.3	8	Natural	24

513 Utility Grade Masking Tape



- Aggressive adhesive
- For applications such as textile, carpet seaming, light industrial, manufacturing, bundling and tabbing

Item Number	Size	Tensile lb/in	Adhesion oz/in	Thickness mils	Elongation %	Color	Rolls/Case
87217	18mm x 54.8m	19	42	5	6.4	Natural	48
87202	24mm x 54.8m	19	42	5	6.4	Natural	36
87218	36mm x 54.8m	19	42	5	6.4	Natural	24
87201	48mm x 54.8m	19	42	5	6.4	Natural	24

Additional products, sizes and specifications available. Log on to www.itape.com to view our complete product offering.



CLOTH/DUCT TAPE

Intertape® brand Cloth/Duct Tapes satisfy even the most demanding requirements and industry standards. A must have for the most discerning contractors and every job site. Applications include sealing, bundling, weatherproofing, convention set-up, entertainment, construction, maintenance, and book binding/repair.



PREMIUM GRADE

AC50 Premium Grade Cloth/Duct Tape



- Provides excellent moisture barrier
- For use when a significant level of tensile and tear strength are required
- Meets ASTM D5486 Type 1

Item Number	Size	Tensile lb/in	Adhesion oz/in	Thickness mils	Elongation %	Color	Rolls/Case
82762	48mm x 54.8m	40	60	14.0	21	Silver	24
82763	48mm x 54.8m	40	60	14.0	21	Black	24

MEDIUM GRADE

AC36 Medium Grade Cloth/Duct Tape



- The general contractor's duct tape of choice
- Aggressive adhesive for high performance applications

Item Number	Size	Tensile lb/in	Adhesion oz/in	Thickness mils	Elongation %	Color	Rolls/Case
82843	48mm x 54.8m	20	50	11.0	18	Silver	24
83053	72mm x 54.8m	20	50	11.0	18	Silver	16
82842	48mm x 54.8m	20	50	11.0	18	Black	24
83052	72mm x 54.8m	20	50	11.0	18	Black	16

UTILITY GRADE

AC20 Utility Grade Cloth/Duct Tape



- Economic all-purpose duct tape for home and office use

Item Number	Size	Tensile lb/in	Adhesion oz/in	Thickness mils	Elongation %	Color	Rolls/Case
74977	48mmx54.8m	18	40	9.0	14	Silver	24
78750	72mmx54.8m	18	40	9.0	14	Silver	16

AC10 Utility Grade Cloth/Duct Tape



- Ideal for wrapping, sealing and general use
- Conforms to irregular shapes

Item Number	Size	Tensile lb/in	Adhesion oz/in	Thickness mils	Elongation %	Color	Rolls/Case
87372	48mmx54.8m	17	41	7.0	15	Silver	24

Additional products, sizes and specifications available. Log on to www.itape.com to view our complete product offering.

Intertape® brand **FILAMENT TAPE**

Intertape® brand fiberglass reinforced Filament Tape delivers superior adhesion for a variety of light to medium load applications. Intertape® brand MOPP Strapping Tape utilizes mono-oriented tensilized polypropylene for light duty strapping, palletizing and bundling.

PREMIUM GRADE

RG16* Premium Grade Filament Tape



- Polyester film backed
- Natural rubber adhesive
- Very high tensile strength
- Ideal for heavy duty industrial applications

Item Number	Size	Tensile lb/in	Adhesion oz/in	Thickness mils	Elongation %	Color	Rolls/Case
RG16...35	18mm x 54.8m	333	36	7.5	4.5	Natural	48
RG16...36	24mm x 54.8m	333	36	7.5	4.5	Natural	36
RG16...37	48mm x 54.8m	333	36	7.5	4.5	Natural	24

RG316* Premium Grade Filament Tape



- BOPP backed
- Thin profile for medium to heavy duty use
- Ideal for moderate industrial packaging

Item Number	Size	Tensile lb/in	Adhesion oz/in	Thickness mils	Elongation %	Color	Rolls/Case
RG316.3	18mm x 54.8m	300	36	6.1	4	Clear	48
RG316.4	24mm x 54.8m	300	36	6.1	4	Clear	36
RG316.5	48mm x 54.8m	300	36	6.1	4	Clear	24

MEDIUM GRADE

RG315* Medium Grade Filament Tape



- BOPP backed with medium tensile strength
- Ideal for palletizing, unitizing and strapping heavier products

Item Number	Size	Tensile lb/in	Adhesion oz/in	Thickness mils	Elongation %	Color	Rolls/Case
RG315.3	18mm x 54.8m	180	37	5.1	4	Clear	48
RG315.4	24mm x 54.8m	180	37	5.1	4	Clear	36
RG315.5	48mm x 54.8m	180	37	5.1	4	Clear	24

RG15 Medium Grade Filament Tape



- Polyester film backed; medium tensile strength
- Aggressive natural rubber adhesive
- Ideal for palletizing, unitizing and bundling heavier products

Item Number	Size	Tensile lb/in	Adhesion oz/in	Thickness mils	Elongation %	Color	Rolls/Case
RG15.27	18mm x 54.8m	175	39	5.6	4	Natural	48
RG15.28	24mm x 54.8m	175	39	5.6	4	Natural	36
RG15.29	48mm x 54.8m	175	39	5.6	4	Natural	24

GENERAL GRADE

RG3 General Grade Filament Tape



- Industry workhorse
- PET polyester film backed multi purpose filament tape

Item Number	Size	Tensile lb/in	Adhesion oz/in	Thickness mils	Elongation %	Color	Rolls/Case
		131	38	5.1	3	Natural	

Additional products, sizes and specifications available. Log on to www.itape.com to view our complete product offering.
* Standard lead times may not apply.



FILAMENT & MOPP TAPE



UTILITY GRADE

RG400* Utility Grade Filament Tape



- Hand tearable
- Readable graphics through contact clear construction
- Excellent delamination resistance for ease of use when having to stop, break and restart a roll
- Excellent for bundling, strapping and palletizing

Item Number	Size	Tensile lb/in	Adhesion oz/in	Thickness mils	Elongation %	Color	Rolls/Case
RG400.12	12mm x 54.8m	100	75	5.3	4	Clear	72
RG400.18	18mm x 54.8m	100	75	5.3	4	Clear	48
RG400.24	24mm x 54.8m	100	75	5.3	4	Clear	36

RG300 Utility Grade Filament Tape



- BOPP backed
- Ideal for non-critical packaging and shipping

Item Number	Size	Tensile lb/in	Adhesion oz/in	Thickness mils	Elongation %	Color	Rolls/Case
RG300.38	9mm x 54.8m	100	48	4.0	3	Clear	96
RG300.39	12mm x 54.8m	100	48	4.0	3	Clear	72
RG300.40	18mm x 54.8m	100	48	4.0	3	Clear	48
RG300.41	24mm x 54.8m	100	48	4.0	3	Clear	36
RG300.43	48mm x 54.8m	100	48	4.0	3	Clear	24

BUNDLING/STRAPPING (MOPP)

197 MOPP Tape



- Used for palletizing, unitizing and bundling
- Temperature resistant to 160°F/70°C

Item Number	Size	Tensile lb/in	Adhesion oz/in	Thickness mils	Elongation %	Color	Rolls/Case
197...4	9mm x 54.8m	95	55	2.7	34	Clear	192
197...5	12mm x 54.8m	95	55	2.7	34	Clear	144
197...7	18mm x 54.8m	95	55	2.7	34	Clear	96
197...13	9mm x 54.8m	95	55	2.7	34	Black	192
197...15	12mm x 54.8m	95	55	2.7	34	Black	144
197...16	18mm x 54.8m	95	55	2.7	34	Black	96

Additional products, sizes and specifications available. Log on to www.itape.com to view our complete product offering.



Intertape[®] brand **FLATBACK TAPE**

Intertape[®] brand Flatback Tape is designed for a variety of packaging, splicing and tabbing applications, providing a quick, positive seal under a wide range of temperature and humidity conditions. Applications include splicing, tabbing and box closure.



MEDIUM GRADE

PM2 Flatback Tape



- Versatile
- Matches most corrugated cardboard for professional sealed look

Item Number	Size	Tensile lb/in	Adhesion oz/in	Thickness mils	Elongation %	Color	Rolls/Case
PM2...74	24mm x 54.8m	36	57	6.0	3	Tan	36
PM2...75	36mm x 54.8m	36	57	6.0	3	Tan	24
PM2...77	48mm x 54.8m	36	57	6.0	3	Tan	24

539 Flatback Tape



- Low curl; highly conformable tape
- Designed for carton sealing, splicing and use with automatic tape heads

Item Number	Size	Tensile lb/in	Adhesion oz/in	Thickness mils	Elongation %	Color	Rolls/Case
74936	18mm x 54.8m	45	60	7.2	7	Brown	48
74937	24mm x 54.8m	45	60	7.2	7	Brown	36
74938	36mm x 54.8m	45	60	7.2	7	Brown	24
74941	48mm x 54.8m	45	60	7.2	7	Brown	24

534 Flatback Tape



- Low curl; highly conformable tape
- Designed for carton sealing, splicing and use with automatic tape heads

Item Number	Size	Tensile lb/in	Adhesion oz/in	Thickness mils	Elongation %	Color	Rolls/Case
71598	24mm x 54.8m	40	50	7.2	7	Brown	36
71624	36mm x 54.8m	40	50	7.2	7	Brown	24
71672	48mm x 54.8m	40	50	7.2	7	Brown	24

Additional products, sizes and specifications available. Log on to www.itape.com to view our complete product offering.





DOUBLE-COATED TAPE

Intertape® brand Double-Coated Tape features an extremely aggressive tack. Ideal for many industrial uses such as golf grip application, photograph mounting, carpet installation, plate mounting, and adhering and bonding applications.



UTILITY GRADE

591 Double-Coated Tape



- Standard for golf grip repair
- Heavy duty; double-coated flatback
- Also ideal for photograph mounting, carpet installation and textile manufacturing

Item Number	Size	Tensile lb/in	Adhesion oz/in	Thickness mils w/o liner/with liner	Elongation %	Color	Rolls/Case
72699	18mm x 32.9m	34	64	7.0/12.0	3	Natural	48
72706	24mm x 32.9m	34	64	7.0/12.0	3	Natural	36
72713	36mm x 32.9m	34	64	7.0/12.0	3	Natural	24
84913	2in x 36yds	34	64	7.0/12.0	3	Natural	24

592 Double-Coated Tape



- Double-coated crepe paper tape w/ white liner
- Easy-release treated
- Ideal for printing/textile industry and certain splicing applications

Item Number	Size	Tensile lb/in	Adhesion oz/in	Thickness mils w/o liner/with liner	Elongation %	Color	Rolls/Case
82738	18mm x 32.9m	23	47	6.0/10.4	8.5	Natural	48
82739	24mm x 32.9m	23	47	6.0/10.4	8.5	Natural	36
82741	48mm x 32.9m	23	47	6.0/10.4	8.5	Natural	24

Additional products, sizes and specifications available. Log on to www.itape.com to view our complete product offering.



COMPLEMENTARY PRODUCTS

PRESSURE-SENSITIVE CARTON-SEALING TAPE

As a leader in the pressure-sensitive carton-sealing tape market, Intertape Polymer Group™ (IPG) combines years of experience as a prime manufacturer of superior quality tape to the industrial and consumer channels.



HOT MELT ADHESIVE

Intertape® brand Hot Melt Adhesive Carton-Sealing Tapes offer the widest range of application flexibility available. Superior adhesion properties, holding force and tensile strength ensure consistent, reliable seals. Noted for quiet release and easy unwind, IPG's Hot Melt Tape is well suited for automatic case-sealing machines.



ACRYLIC ADHESIVE

Intertape® brand Acrylic Carton-Sealing Tape is best suited for applications in temperatures less than 40°F and greater than 120°F. Providing excellent clarity, acrylic tape ages well over extended periods in sunlight and fluorescent lighting.



NATURAL RUBBER ADHESIVE

Central® brand Natural Rubber Tape has the most aggressive adhesive available offering fast, positive bonding on “problem” applications such as high recycled content cartons, rough or ultra-smooth cartons, heavy ink coverage, dusty and/or dirty environments, humid conditions and temperature extremes.

WATER-ACTIVATED CARTON-SEALING TAPE

Central® brand Water-Activated Tapes bond instantly to both virgin and recycled fiber (corrugated carton, paper, etc.) surfaces and therefore, generate an immediate destructive bond resulting in a tamper evident package. Central is a recognized pioneer and innovator in water-activated technology.



REINFORCED

Available in a wide variety of sizes and product construction, Central® Brand reinforced tapes are designed to provide consistent performance in carton sealing applications where durability, extra strength and reliability are required. Extra strong fiberglass yarns are bonded between the high tensile strength sheets for an extra margin of strength.



PAPER

Designed for fast, permanent adhesion and superior strength. Cracking of the adhesive surface provides our paper tape with excellent flexibility for sealing carton corners, edges and irregular surfaces. Use Central® Brand paper tapes to seal lightweight or standard sized packages or cartons that will be shipped in unitized loads or full pallets. Central® Brand paper tapes are Lili™ Approved as the most environmentally preferred method of sealing a box.



COMPLEMENTARY PRODUCTS



FILMS

STRETCH FILM

A market leader in technology, IPG manufactures monolayer and 3-layer blown film, both 5 & 7-layer cast films and specialty products on state-of-the-art equipment in ISO Certified facilities.

SuperFLEX™ brand High Performance Films provide significant downgauging opportunities yielding as much as a 30% reduction in the amount of film needed to securely contain a load. In addition to providing a measurable cost savings, the reduction in film consumed means that SuperFLEX™ brand films are environmentally preferred over conventional films.

StretchFLEX® brand Stretch Wrap rounds out the Intertape Polymer Group line of films and is designed to meet a variety of stretch wrapping needs.



SHRINK FILM

Exfilm® brand shrink films guarantee your packaging looks its absolute best, while providing unmatched durability, versatility and value. Our advanced crosslinking technology enables sealing on all types of equipment across a wider range of temperatures, and improves burn through resistance ensuring the best possible package.



PROTECTIVE PACKAGING

For years, Intertape Polymer Group has been a trusted source for the products that secure your packages as a leading supplier of carton-sealing tapes and stretch film. It only makes sense that you would also rely on Intertape to protect the contents of your packages. That is why the iCushion™ brand Protective Packaging line emerged with the fastest Air Pillow System on the market and continues to expand.



AP-2000 Inflatible Air Pillow System

AP-8000C INFLATABLE AIR PILLOW SYSTEM

- Available in conventional or Oxo-Biodegradable film
- Popular pillow sizes: 8" x 8" and 8" x 12"

AP-2000 INFLATABLE AIR PILLOW SYSTEM

- Available in Oxo-Biodegradable film
- Popular pillow sizes: 8" x 4" and 8" x 8"

Placement of air pillow systems requires customer commitment.



NOW AVAILABLE IN AN OXO-BIODEGRADABLE FORMULATION!

iCushion™ Oxo-biodegradable air pillows are available in a variety of popular sizes.



COMPLEMENTARY PRODUCTS

CASE SEALING EQUIPMENT

IPG's Interpack™ brand of quality case sealers and accessories offers the features and versatility you need with performance you can depend on... all at the most cost-effective price. Our comprehensive equipment line includes case sealers, tape heads, case erectors, standard and special options and custom-built special application machinery.

Case sealing equipment available in:

- USA Series - Uniform Semi-Automatic
- UA Series - Uniform Automatic
- RSA Series - Random Semi-Automatic
- RA Series - Random Automatic



USA 3036-SB Case Sealer

Ask about Interpack's equipment capabilities and programs... including the Tape Head Program, Tape Incentive Program, Parts Voucher, Spare Parts Kit and more.



WATER-ACTIVATED TAPERS

As the market leader for water-activated carton-sealing tape, Intertape's commitment continues with the introduction of state-of-the-art tabletop dispensers.

This superior line of dispensers offers improved features and benefits enhancing the value created by an integrated system of closure material and dispenser. The increased capabilities highlighted in the TWA 1000-M Manual Taper and TWA 1000-E Electric Taper provide the quality your production requires.



TWA 1000-M Manual Taper

TWA 1000-E Electric Taper

CARTON-SEALING TAPE HAND DISPENSERS

Intertape brand carton-sealing tape hand dispensers have a comfortable pistol grip and adjustable tension brake. Available for 2 and 3-inch rolls of tape.



MEET LILI™

Lili™ is Intertape's environmental stewardship program and stands for "Low environmental impact line from Intertape". Lili™ encompasses:

- Corporate Commitment
- Socially Responsible Corporate Initiatives

LILI APPROVED PRODUCTS


- Oxo-Biodegradable Films, including Stretch Film, Shrink Film and Air Pillows
- Central® brand Water-Activated Paper Tape





CORPORATE PROFILE

Intertape Polymer Group Inc. (IPG) is an acknowledged leader in the packaging industry. Leveraging its advanced manufacturing and technologies, extensive research and development capabilities and a comprehensive strategic acquisition program, the company believes it has assembled the broadest and deepest range of products in the industry. IPG is widely recognized for its development and manufacture of specialized polyolefin, plastic and paper-based packaging products, as well as complementary packaging systems for industrial and retail use. Additionally, IPG is a woven and flexible intermediate bulk container (FIBC) manufacturer. Its performance products, including tapes and cloths, are designed for demanding aerospace, automotive and industrial applications and are sold to a broad range of industry/specialty distributors, retail stores and large end-users in diverse industries.



Porto, Portugal

Flensburg, Germany



- Manufacturing
- ▲ Distribution
- ipg Offices



Toll Free: **800-IPG-8273 / 800-474-8273**

Marysville, MI Fax: 800-368-8273 | Columbia, SC Fax: 800-462-1293 | Montreal, QC Fax: 800-561-3671

Tape Technical Help: 877-447-4832 | www.itape.com | E-mail: info@itape.com

Follow Us On Facebook
www.facebook.com/intertape