

1970

3" WIDE HAND DISPENSER, WITH PISTOL GRIP AND TENSION BRAKE

INTERTAPE POLYMER GROUP TECHNICAL DATA SHEET

PRODUCT FEATURES

- Reinforced Steel Frame
- High Impact Plastic
- Heat Treated Steel Blade
- Adjustable Tension Brake
- Plastic Tension Control Knob
- Plastic Wipe Down Blade
- Plastic Loading Gate
- Baked Paint Finish
- Natural rubber Tape Roller
- Also Available in 2" Dispenser (1969)

APPLICATION

For ease in manual box sealing, packaging and shipping applications.

PRODUCT PACKAGING

24 Dispensers/Case
22 Cases/Pallet



3647 Cortez Road West | Bradenton, FL 34210 | USA
Customer Service: 800.IPG.8273 | 800.474.8273
Tape Technical Service: 877.447.4832
www.intertapepolymer.com | info@itape.com

PHYSICAL PROPERTIES

Height	10.875" (276 mm)
Width	6.875" (174 mm)
Depth	3.5" (89 mm)

MAXIMUM TAPE SIZE CAPABILITY

Outside Dimension	5.75" (146 mm)
Roll Width	3.0" (76 mm)
Core Diameter	3.0" (76 mm)



While we believe them to be reliable, the statements and information herein are only for general guidance and are not warrants or guarantees for accuracy and completeness. The user must, by test or otherwise, determine suitability for this purpose. There is no warranty of fitness for a particular purpose. Our standard term and conditions of sale apply exclusively to all orders, and all liability for damages of any kind, including consequential, exceeding purchase price is excluded. No one is authorized by us to make oral warranties. We reserve the right to make changes without notice or obligation in our products and publications.

EFFECTIVE: 5/09