

# PIG® HazMat Mat Roll

#MAT325 - Light-weight • 30" x 300'



Lasts 2x longer than ordinary mats for fewer change-outs.  
Specially made for acids, bases, corrosives and chemical spills.

- Absorbs the widest range of acids, bases, corrosives, chemicals and unknown liquids - even those with high concentrations like 98% sulfuric acid and 30% sodium hydroxide
- Chemical-resistant mat won't degrade or cause a dangerous reaction upon contact with corrosive spills
- Eight layers of 100% polypropylene are thermally bonded to make PIG Mat the strongest mat on the market; won't rip, tear or fray even when saturated
- Exclusive dimple pattern speeds wicking of liquid throughout mat for faster, easier cleanup
- Highly absorbent, fine-fiber construction won't leave behind liquids or fiber residue
- Pink color is easily distinguishable to assure workers use the correct mat during a spill emergency
- Flame-resistant material won't burn immediately like cellulose mats; melts when exposed to high heat while on the job
- Rolls are ideal for covering large areas and soaking up spills
- Light-weight mat is ideal for small cleanups and light-duty tasks

Always in stock. Ships within 24 hours.



**New Pig**

By Phone:  
**1-855-493-HOGS**

Online:  
**[newpig.com](http://newpig.com)**

Email:  
**[hothogs@newpig.com](mailto:hothogs@newpig.com)**

One Pork Avenue • Tipton PA 16684-0304

© 2014 New Pig Corporation. All rights reserved.  
PIG and the PIG logo are trademarks in the U.S. and other countries.

ITEM: MAT325 - Pg 1 of 2

## MAT325 Specifications

<b>Color:</b>	Pink
<b>Dimensions:</b>	30" W x 300' L
<b>Mat Weight:</b>	Light-weight
<b>Fluids Absorbed:</b>	Acids, Bases & Unknowns
<b>Absorbency:</b>	Up to 40 gal. per bag
<b>Absorbency per:</b>	Up to 40 gal. per roll
<b>Dispenser:</b>	No
<b>Perforated:</b>	Every 10" Lengthwise & Centered Widthwise
<b>Poly-Backing:</b>	No
<b>UV Resistant:</b>	No
<b>Sold as:</b>	1 roll per bag
<b>Weight:</b>	30 lbs.
<b># per Pallet:</b>	12
<b>Composition:</b>	100% Polypropylene
<b>UNSPSC:</b>	47131901

## Technical Information

### Warnings & Restrictions:

There are no known warnings and restrictions for this product.

### Technical Documents:

(Available at [newpig.com](http://newpig.com))

Product Data Sheet (PDS)

Safety Data Sheet (SDS)

Chemical Compatibility (CCG)



## MAT325 Metric Equivalent

<b>Dimensions:</b>	76.2cm W x 91m L
<b>Absorbency:</b>	Up to 151.4 L per bag
<b>Absorbency per:</b>	Up to 151.4 L per roll
<b>Weight:</b>	13.6 kg



**New Pig**

By Phone:  
**1-855-493-HOGS**

Online:  
**[newpig.com](http://newpig.com)**

Email:  
**[hothogs@newpig.com](mailto:hothogs@newpig.com)**

One Pork Avenue • Tipton PA 16684-0304

© 2014 New Pig Corporation. All rights reserved.  
PIG and the PIG logo are trademarks in the U.S. and other countries.

ITEM: MAT325 - Pg 2 of 2