

Nashua®
TAPE PRODUCTS **557**
UL181B-FX Cloth Duct Tape





Nashua® TAPE PRODUCTS 557

UL181B-FX Cloth Duct Tape

Berry Plastics Corporation, the industry leader for innovative materials for HVAC, is proud to offer **Nashua® 557** UL181B-FX Cloth Duct Tape. Designed to meet the needs of virtually all duct sealing applications, 557 is UL Listed for use on **flexible duct** installations.

SPECIAL FEATURES

- UL181B-FX Listed - Printed for easy identification
- Provides an excellent long-term bond
- Mold Resistant
- Humidity Resistant
- Good all temperature performance
- Low VOC
- Can contribute toward EA Credit 1 (Optimize Energy Performance) and EQ Credit 4.1 (Low Emitting Materials, Adhesives and Sealants) under LEED®

Thickness: 14 mils (355.60 μ)

Adhesion to Steel: 45 oz/in (4.93 N/cm)

Adhesion to Backing : 35 oz/in (3.83 N/cm)

Tensile Strength: 29 lb/in (50.79 N/cm)

Installation Temperature: 40 to 100 °F (4 to 37°C)

Operating Temperature: 30 to 200 °F (-1 to 93°C)

VOC Content: <1 g/L

**FOR MORE INFORMATION ON
NASHUA® 557 OR OTHER NASHUA® BRAND PRODUCTS
FOR THE HVAC MARKET, CONTACT YOUR AREA SALES
REPRESENTATIVE.**



Visit our website
to learn more!

SILVER

ITEM NO. 5570020008A
Size 48mm x 55M
24 rolls/case 27 cases/pallet
UPC: 033656379558

ITEM NO. 5570020008A
Size 72mm x 55M
16 rolls/case 27 cases/pallet

BLACK

ITEM NO. 5579020008A
Size 48mm x 55M
24 rolls/case 27 cases/pallet
UPC: 742366000170

ITEM NO. 5570030008A
Size 72mm x 55M
16 rolls/case 27 cases/pallet
UPC: 742366001191

METALLIC

ITEM NO. 557004A
Size 48mm x 55M
24 rolls/case 27 cases/pallet
UPC: 742366999672

ITEM NO. 557003A
Size 72mm x 55M
16 rolls/case 27 cases/pallet
UPC: 742366001184

For more information:
25 Forge Parkway
Franklin, MA 02038
Phone 508.918.1600 • Fax 508.918.1901
Toll Free US: 1.800.343.7875

 TM
tapes.berryplastics.com