



# LOCTITE<sup>®</sup> N-7000<sup>™</sup> Metal Free, High Purity Anti-Seize

April 2010

## PRODUCT DESCRIPTION

LOCTITE<sup>®</sup> N-7000<sup>™</sup> Metal Free, High Purity Anti-Seize provides the following product characteristics:

<b>Technology</b>	Anti-Seize
<b>Chemical Type</b>	Calcium Oxide/Graphite Based
<b>Appearance</b>	Dark gray paste <sup>LMS</sup>
<b>Components</b>	One component - requires no mixing
<b>Cure</b>	Non-curing
<b>Application</b>	Lubrication

LOCTITE<sup>®</sup> N-7000<sup>™</sup> Metal Free, High Purity Anti-Seize is a specially formulated metal-free anti-seize lubricant, produced under 100% controlled conditions for the highest purity. It is formulated with high purity raw materials and contains only trace levels of halogens, sulfur, copper, aluminum and heavy metals. Developed to protect steel, stainless steel and other proprietary alloys. During assembly, it prevents high friction, galling and seizing and promotes uniform and predictable clamping. During operation, the high purity prevents stress corrosion. During disassembly, it prevents seizing, galling and destruction of threads. It provides significant improvement in anti-seize performance and gives it more uniform torque tension. Typical applications includes bolts, valves, studs, pipe fittings, slip fits and press fits in nuclear electric power generating plants, chemical plants, pharmaceutical plants, paper mills and other locations where stainless steel fasteners are used. This product is typically used in applications with an operating range of -29 °C to +1315 °C.

## TYPICAL PROPERTIES

Specific Gravity @ 25 °C	1.12 to 1.27 <sup>LMS</sup>
Penetration, ISO 2137, unworked, 1/10 mm	320 to 380 <sup>LMS</sup>
Weight Per Gallon, lbs/gal	9.3 to 10.3
Flash Point - See MSDS	
Ionic Contaminants, ppm:	
Chloride	≤50 <sup>LMS</sup>
Fluorine	≤200 <sup>LMS</sup>
Sulfur	≤100 <sup>LMS</sup>
Lead	≤25 <sup>LMS</sup>
Cadmium	≤2 <sup>LMS</sup>
Tin	≤200 <sup>LMS</sup>
Zinc	≤25 <sup>LMS</sup>
Copper	≤50 <sup>LMS</sup>
Mercury	≤5 <sup>LMS</sup>

## TYPICAL PERFORMANCE

An anti-seize lubricant used on a bolt helps to develop greater clamp load for the same torque compared to an unlubricated bolt. An additional benefit is greater uniformity in clamp load among a series of bolts. The relationship between torque and clamp load is expressed in the following equation:

$$T = K \times F \times D$$

**T** = Torque (N-m, lb.in, lb.ft)

**K** = Torque coefficient or nut factor, determine experimentally

**F** = Clamp load (N, lb.)

**D** = Nominal diameter of bolt (mm, in.)

Torque coefficient, k:

12.7 mm steel bolts (grade 8) and nuts (grade 5)	0.16
12.7 mm 304 stainless steel bolts (grade 8) and nuts (grade 5)	0.18
12.7 mm steel bolts (grade 8) and nuts (grade 5), solvent cleaned, not lubricated	0.27

## GENERAL INFORMATION

**This product is not recommended for use in pure oxygen and/or oxygen rich systems and should not be selected as a lubricant for chlorine or other strong oxidizing materials.**

**For safe handling information on this product, consult the Material Safety Data Sheet (MSDS).**

## Handling precautions

LOCTITE<sup>®</sup> N-7000<sup>™</sup> Metal Free, High Purity Anti-Seize contains calcium derivatives and may not be compatible with some lithium based products. Therefore, all areas of application must be thoroughly cleaned before applying.

## Directions for use:

1. Before or during assembly, wipe or brush onto threads and other joint surfaces needing protection.
2. Use full strength. Do not thin.

## Loctite Material Specification<sup>LMS</sup>

LMS dated April 01, 2010. Test reports for each batch are available for the indicated properties. LMS test reports include selected QC test parameters considered appropriate to specifications for customer use. Additionally, comprehensive controls are in place to assure product quality and consistency. Special customer specification requirements may be coordinated through Henkel Quality.

**Storage**

Store product in the unopened container in a dry location. Storage information may be indicated on the product container labeling.

**Optimal Storage: 8 °C to 21 °C. Storage below 8 °C or greater than 28 °C can adversely affect product properties.**

Material removed from containers may be contaminated during use. Do not return product to the original container. Henkel Corporation cannot assume responsibility for product which has been contaminated or stored under conditions other than those previously indicated. If additional information is required, please contact your local Technical Service Center or Customer Service Representative.

**Conversions**

$(^{\circ}\text{C} \times 1.8) + 32 = ^{\circ}\text{F}$

$\text{kV/mm} \times 25.4 = \text{V/mil}$

$\text{mm} / 25.4 = \text{inches}$

$\mu\text{m} / 25.4 = \text{mil}$

$\text{N} \times 0.225 = \text{lb}$

$\text{N/mm} \times 5.71 = \text{lb/in}$

$\text{N/mm}^2 \times 145 = \text{psi}$

$\text{MPa} \times 145 = \text{psi}$

$\text{N}\cdot\text{m} \times 8.851 = \text{lb}\cdot\text{in}$

$\text{N}\cdot\text{m} \times 0.738 = \text{lb}\cdot\text{ft}$

$\text{N}\cdot\text{mm} \times 0.142 = \text{oz}\cdot\text{in}$

$\text{mPa}\cdot\text{s} = \text{cP}$

**Note**

The data contained herein are furnished for information only and are believed to be reliable. We cannot assume responsibility for the results obtained by others over whose methods we have no control. It is the user's responsibility to determine suitability for the user's purpose of any production methods mentioned herein and to adopt such precautions as may be advisable for the protection of property and of persons against any hazards that may be involved in the handling and use thereof. In light of the foregoing, **Henkel Corporation specifically disclaims all warranties expressed or implied, including warranties of merchantability or fitness for a particular purpose, arising from sale or use of Henkel Corporation's products. Henkel Corporation specifically disclaims any liability for consequential or incidental damages of any kind, including lost profits.** The discussion herein of various processes or compositions is not to be interpreted as representation that they are free from domination of patents owned by others or as a license under any Henkel Corporation patents that may cover such processes or compositions. We recommend that each prospective user test his proposed application before repetitive use, using this data as a guide. This product may be covered by one or more United States or foreign patents or patent applications.

**Trademark usage**

Except as otherwise noted, all trademarks in this document are trademarks of Henkel Corporation in the U.S. and elsewhere. ® denotes a trademark registered in the U.S. Patent and Trademark Office.

Reference 1.1