



Available Colors: Black



Better **Best** **Superior**



Oct-O-Flex™ is a heavy duty outdoor entrance mat made with tough SBR rubber to remain flexible and withstand extreme cold weather conditions. The unique design has holes to drain water and debris away from the entrance, while the smooth top surface and beveled edges on all four sides make it wheel chair and cart friendly. A raised knobbed underside combined with the weight of the mat helps to eliminate mat movement.

| Test | Test Description | *Results |
|-----------------------------|--|--|
| ASTM D-3884-01 | Abrasion Resistance | @ 1000 cycles: 2.70 grams (3.30%) |
| ASTM C-1028-96 | Static Coefficient of Friction | Wet: 0.69 Dry: 0.72 |
| ASTM D-575 | Compression Deflection | @ 25%: 39.6 lbs./in ² @ 50% 149.8 lbs./in ² |
| ASTM D-1171 | Ozone (Method A) | No Noticeable Effect |
| CPSC FF 1-70 ASTM D-2859 | Surface Flammability of Carpets and Rugs Ignition Characteristics - Finished Textile Floor Covering Material | Pass |

*All testing of NoTrax® floor matting has been performed by an independent testing laboratory.

12/2014



Drainage



Outdoor

- Resilient rubber compound
- Multi-hole drainage system channels water and debris away from walking surface
- Raised knob underside provides aeration, reduces mat movement
- Thickness: 1/2"
- Molded beveled edging on all 4 sides
- Stock Sizes: 2' x 3', 3' x 5', 4' x 6'