


# Fully Packaged Air Compressors

**SPEEDAIRE**<sup>®</sup>

One System. One Brand. One Source.



**Exclusively from Grainger.**

Call or visit your local branch or go to [grainger.com/speedaire](http://grainger.com/speedaire) for complete product line information

## Fully Packaged Air Compressors

Our line of 80 and 120 gallon vertical and horizontal, fully packaged compressors features isolation pads, an after cooler and automatic electronic tank drain. In addition to a 3 year Pump & Tank Warranty, these units come with on-site service and each unit is UL/CSA Rated. The units also feature a magnetic starter that has thermal protection for the motor and come with an ASME certified tank. With premium efficiency motors options ranging from 5 to 15 HP, a mix of 1 and 3 Phase units and a range of SCFM and PSI ratings, this line of fully packaged compressors are designed to meet a wide range of customer needs.

### 80 Gallon Horizontal



**35WC44**

**35WC46**

Max PSI: 175  
 3 Year Pump & Tank Warranty  
 80/20 Max Duty Cycle  
 Tank Outlet 3/4 in(F)NPT  
 Recommended Oil:

- 2 qt.** Single viscosity SAE 30 ISO100 nondetergent synthetic compressor oil  
 Grainger Part Number 1WG49
- 2 qt.** Single viscosity SAE 30 ISO 100 nondetergent mineral compressor oil  
 Grainger Part Number 4ZF21



**35WC52**

Max PSI: 175  
 3 Year Pump & Tank Warranty  
 80/20 Max Duty Cycle  
 Tank Outlet 3/4 in(F)NPT  
 Recommended Oil:

- 2 qt.** Single viscosity SAE 30 ISO100 nondetergent synthetic compressor oil  
 Grainger Part Number 1WG49
- 2 qt.** Single viscosity SAE 30 ISO 100 nondetergent mineral compressor oil  
 Grainger Part Number 4ZF21

SKU NO.	HORSEPOWER	POWER	PHASE	DISPLACEMENT CFM	AIR DELIVERY CFM@MAX PSI	MAX PSI	PUMP (RPM)	PUMP LIFE	UNIT WEIGHT (LBS.)	AMP DRAW	UNIT DIMENSIONS (IN.)		
											L	W	H
<b>80 Gallon, Horizontal Compressors</b>													
<b>35WC44</b>	5	208-230V	1	21.1	16.4	175	700	15,000 hrs	510	22	63	21	46
<b>35WC46</b>	5	208- 230/460V	3	21.1	16.4	175	700	15,000 hrs	510	14.2- 12.8/6.4	63	21	46
<b>35WC52</b>	7.5	208-230V	3	31.4	24.5	175	1020	15,000 hrs	540	19.8- 17.9/9	63	21	46

Call or visit your local branch or go to [grainger.com/speedaire](http://grainger.com/speedaire)  
 for complete product line information



Exclusively from Grainger.

## 80 Gallon Vertical



Max PSI: 175  
 3 Year Pump & Tank Warranty  
 80/20 Max Duty Cycle  
 Tank Outlet 3/4 in(F)NPT  
 Recommended Oil:

**16 oz.** Single viscosity SAE 30 ISO100 nondetergent synthetic compressor oil  
 Grainger Part Number 1WG49

**16 oz.** Single viscosity SAE 30 ISO 100 nondetergent mineral compressor oil  
 Grainger Part Number 4ZF21



Max PSI: 175  
 3 Year Pump & Tank Warranty  
 80/20 Max Duty Cycle  
 Tank Outlet 3/4 in(F)NPT  
 Recommended Oil:

**2 qt.** Single viscosity SAE 30 ISO100 nondetergent synthetic compressor oil  
 Grainger Part Number 1WG49

**2 qt.** Single viscosity SAE 30 ISO 100 nondetergent mineral compressor oil  
 Grainger Part Number 4ZF21

## 90 Gallon Vertical



Max PSI: 175  
 3 Year Pump & Tank Warranty  
 80/20 Max Duty Cycle  
 Tank Outlet 3/4 in(F)NPT  
 Recommended Oil:

**4 qt.** Single viscosity SAE 30 ISO100 nondetergent synthetic compressor oil  
 Grainger Part Number 1WG47

**4 qt.** Single viscosity SAE 30 ISO 100 nondetergent mineral compressor oil  
 Grainger Part Number 4ZF21

SKU NO.	HORSEPOWER	POWER	PHASE	DISPLACEMENT CFM	AIR DELIVERY CFM@MAX PSI	MAX PSI	PUMP (RPM)	PUMP LIFE	UNIT WEIGHT (LBS.)	AMP DRAW	UNIT DIMENSIONS (IN.)		
											L	W	H
<b>80 Gallon, Vertical Compressors</b>													
<b>35WC43</b>	5	230 V	1	21.1	16.4	175	700	15,000 hrs	510	22	35	27	71
<b>35WC45</b>	5	208- 230/460V	3	21.1	16.4	175	700	15,000 hrs	510	14.2- 12.8/6.4	35	27	71
<b>35WC50</b>	7.5	208-230V	1	31.4	24.5	175	1020	15,000 hrs	540	31	35	27	71
<b>35WC51</b>	7.5	208- 230/460V	3	31.4	24.5	175	1020	15,000 hrs	540	19.8- 17.9/9	35	27	71
<b>90- Gallon, Vertical Compressor</b>													
<b>35WC68</b>	10	208- 230/460V	3	43.1	36.0	175	700	15,000 hrs	875	27- 24.4/12.2	69	24	52

Call or visit your local branch or go to [grainger.com/speedaire](http://grainger.com/speedaire)  
 for complete product line information



Exclusively from Grainger.

## 120 Gallon Horizontal



35WC58

35WC55

Max PSI: 175  
 3 Year Pump & Tank Warranty  
 80/20 Max Duty Cycle  
 Tank Outlet 3/4 in(F)NPT  
 Recommended Oil:

- 4 qt.** Single viscosity SAE 30 ISO100 nondetergent synthetic compressor oil Grainger Part Number 1WG49
- 4 qt.** Single viscosity SAE 30 ISO 100 nondetergent mineral compressor oil Grainger Part Number 4ZF21



35WC56

Max PSI: 175  
 3 Year Pump & Tank Warranty  
 80/20 Max Duty Cycle  
 Tank Outlet 3/4 in(F)NPT  
 Recommended Oil:

- 4 qt.** Single viscosity SAE 30 ISO100 nondetergent synthetic compressor oil Grainger Part Number 1WG49
- 4 qt.** Single viscosity SAE 30 ISO 100 nondetergent mineral compressor oil Grainger Part Number 4ZF21



35WC71

35WC72

35WC73

Max PSI: 175  
 3 Year Pump & Tank Warranty  
 80/20 Max Duty Cycle  
 Tank Outlet- 1 in (F)NPT  
 Recommended Oil:

- 6 qt.** Single viscosity SAE 30 ISO100 nondetergent synthetic compressor oil Grainger Part Number 1WG49
- 6 qt.** Single viscosity SAE 30 ISO 100 nondetergent mineral compressor oil Grainger Part Number 4ZF21

SKU NO.	HORSEPOWER	POWER	PHASE	DISPLACEMENT CFM	AIR DELIVERY CFM@MAX PSI	MAX PSI	PUMP (RPM)	PUMP LIFE	UNIT WEIGHT (LBS.)	AMP DRAW	UNIT DIMENSIONS (IN.)		
											L	W	H
<b>120 Gallon, Horizontal Compressors</b>													
35WC58	10	208	3	43.1	36.0	175	700	15,000 hrs	835	28.1	69	27	54
35WC55	10	208- 230/460V	3	43.1	36.0	175	700	15,000 hrs	835	27- 24.4/12.2	69	27	54
35WC56	15	208- 230/460	3	62.8	50.0	175	1020	15,000 hrs	910	41.1-37.2 18.6	69	27	54
35WC71	20	208- 230/460V	3	76.6	62.0	175	520	15,000 hrs	2100	54.6- 49.4/24.7	72	38	64
35WC72	25	208- 230/460V	3	103	84.0	175	700	15,000 hrs	2100	66.1- 59.8/29.9	72	38	64
35WC73	30	208- 230/460V	3	125.2	95.0	175	850	15,000 hrs	2100	78.3- 70.8/35.4	72	38	64