





Good පිළඳීර්මර Best Superior



Cushion-Dek™ is made from a tough PVC compound molded with a raised pyramid deign to enhance traction. Slotted perforations allow for moisture to drain from the worker platform in wet environments. A studded bottom surface raises the mat and allows for channeling of moisture. The 422 version comes with a thick gritted layer applied to the top surface for extremely slippery environments.

<u>Test</u>	Test Description	* <u>Results</u>
Compression Deflection	Test specimen is subjected to varying compression load levels and the resulting deflection was measured. The greater the deflection, the better the anti-fatigue properties. (Inches)	(420) .093" (40 lbs/sq. inch) (422) .654" (40 lbs/sq. inch)
Coefficient of Friction ASTM C1028-96	A neolite heel assembly with a predetermined load is pulled horizontally with a dynamometer to measure the force required to cause the assembly to slip.	(420) .70 (422) .67
Abrasion Resistance ASTM D3884-01	Test specimen is subjected to the rubbing action of two abrading wheels under controlled conditions. Results measured in Weight loss (Grams)	(420) 2.29 Grams (422) 2.33 Grams
Elongation ASTM D412	Test specimen is stretched at a specified rate until breaking point. The results are measured in % of size increase at breaking point.	N/A
Critical Radiant Flux ASTM E648-94A	The test result is an average critical radiant flux (watts/square cm) which indicates the level of radiant heat energy required to sustain flame propagation in the flooring system.	(420) .41 watts/square cm

^{*}All testing of NoTrax® floor matting has been performed by an independent testing laboratory.



Anti-Fatigue



Anti-Slip



Drainage

• Slotted Perforations: 1/2" wide by 1-7/8" long

• Overall thickness: 7/16"

 Stock Sizes: 2' x 3', 2' x 6', 3' x 4', 3' x 6', 3" x 10', 4' x 6', 4' x 8'

• Roll Sizes: 2' x 30', 3' x 30', 4' x 30'

• Custom sizes available in 2', 3', and 4' widths

 Modular design allows for factory-assembled custom configurations

