

# Pneumatics

## AIR COMPRESSORS



### 5-GALLON SINGLE STAGE AIR COMPRESSOR

The hand carry 5-gallon air compressor features twin 2.5-gallon air tanks, single-stage splash-lubricated compressor pump with cast-iron cylinders and Honda engine with recoil start. Includes regulator and two gauges for tank and outlet pressure.

SKU NO.	HP	CFM @ 90 PSI	AIR TANK	STARTER TYPE	STAGE	OUTLET	DIMENSIONS (IN.)			UNIT WT (LBS.)
							L	W	H	
<b>5-GALLON, SINGLE STAGE AIR COMPRESSOR</b>										
4GB42	4	4.8	5 gallon hand carry	Recoil	Single	1/4"	21	17.5	22.25	77



4GB42

### 8-GALLON SINGLE OR TWO-STAGE AIR COMPRESSORS

The 8-gallon portable air compressors feature twin 4-gallon air tanks, single or two-stage splash-lubricated cast-iron compressor pumps and a Honda engine with recoil start and low-oil shutdown. Includes regulator and two gauges for tank and outlet pressure.

SKU NO.	HP	CFM @ 90 PSI	AIR TANK	STARTER TYPE	STAGE	OUTLET	DIMENSIONS (IN.)			UNIT WT (LBS.)
							L	W	H	
<b>8-GALLON, SINGLE OR TWO-STAGE AIR COMPRESSORS</b>										
1VN93	6.5	13.9	8 gallon portable	Recoil	Single	3/8"	44.5	18.5	27	175
2YJ61	9	18.3	8 gallon portable	Recoil	Two	3/8"	44	26	31	260



2YJ61

### 20-GALLON TWO-STAGE AIR COMPRESSOR

The portable air compressor features a 20-gallon ASME-coded air tank, two-stage splash-lubricated compressor pump with cast-iron cylinders and a Honda engine with recoil start. Includes regulator and two gauges for tank and outlet pressure. Also features a heavy-duty base plate and 14-gauge belt guard to reduce vibration.

SKU NO.	HP	CFM @ 90 PSI	AIR TANK	STARTER TYPE	STAGE	OUTLET	DIMENSIONS (IN.)			UNIT WT (LBS.)
							L	W	H	
<b>20-GALLON, TWO-STAGE AIR COMPRESSOR</b>										
4GB45	9	18.3	20 gallon portable	Recoil	Two	3/8"	46	26	39.5	306



4GB45



The Grainger Choice badge signals a broad selection of products that deliver quality and value, brought to you by Grainger.

## 30-GALLON SINGLE OR TWO-STAGE AIR COMPRESSORS

The air compressors feature a 30-gallon ASME-coded air tank, single or two-stage splash-lubricated compressor pump with cast-iron cylinders and a Honda engine with recoil start. Includes regulator and two gauges for tank and outlet pressure. Also features a heavy-duty base plate and 14-gauge belt guard to reduce vibration.

SKU NO.	HP	CFM @ 90 PSI	AIR TANK	STARTER TYPE	STAGE	OUTLET	DIMENSIONS (IN.)			UNIT WT (LBS.)
							L	W	H	
<b>30-GALLON, SINGLE OR TWO-STAGE AIR COMPRESSORS</b>										
4NB84	6.5	13.9	30 gallon portable	Recoil	Single	3/8"	27.5	27.5	40	244
4NB85	9	18.3	30 gallon stationary	Recoil	Two	3/8"	40	18.5	41.5	306



4NB84




4NB85

## 80-GALLON TWO-STAGE AIR COMPRESSOR

The stationary air compressor features a 80-gallon ASME-coded air tank, two-stage splash-lubricated cast-iron compressor pump and a Honda engine with electric start (battery and cables not included) and low-oil shutdown. Includes regulator and two gauges for tank and outlet pressure. Also features a heavy-duty base plate and 14-gauge belt guard to reduce vibration.

SKU NO.	HP	CFM @ 175 PSI	AIR TANK	STARTER TYPE	STAGE	OUTLET	DIMENSIONS (IN.)			UNIT WT (LBS.)
							L	W	H	
<b>80-GALLON, TWO-STAGE AIR COMPRESSOR</b>										
6EWK7	13	29	80 gallon stationary	Electric	Two	3/8"	52	26.5	53	496



6EWK7

Call or visit your local branch or go to [grainger.com/speedaire](http://grainger.com/speedaire) for complete product line information