




6200SERIES



There's a 6200 for Every Job.

Werner is recognized for a broad product line that provides the best climbing solutions for pro users. Our commitment to safety, productivity, and quality is recognized throughout the industry. Never satisfied with resting on past successes, Werner remains the market leader by continually enhancing and innovating its product offering.



#1 IN LADDERS™

Selecting the Right Ladder.

LADDER STYLE



1 SINGLE-SIDED STEPLADDER

- Industry standard stepladder has now been upgraded
- Includes LOCKTOP™ and EDGE360™



2 TWIN STEPLADDER

- Ideal for two-person jobs
- 300lbs capacity per side
- Includes LOCKTOP™ and EDGE360™



3 PLATFORM LADDER

- Large platform for long standing comfort
- Includes EDGE360™




4 TRIPOD STEPLADDER

- Ideal for tight spaces
- Use between wall studs or hard to reach places
- Access on uneven ground


LADDER HEIGHT

STEPLADDERS



Ladder Height	Maximum Reach
3'	7'
4'	8'
5'	9'
6'	10'
7'	11'
8'	12'
10'	14'
12'	16'

PLATFORM LADDERS





Platform Height	Maximum Reach
2'	8'
4'	10'
6'	12'
8'	14'
10'	16'

The Best Just Got Better.



The 6200 series, trusted by professionals for its durability, is now loaded with new, advanced features to maximize your productivity.

LOCKTOP™ NEXT GENERATION LADDER TOP HOLDS AN ARSENAL OF TOOLS



EDGE 360™

PROTECTION FROM EVERY ANGLE



INTEGRATED RAIL SHIELD

Protects rail during vehicle off-loading and maneuvering on the jobsite



EDGE BRACING

Supports rail and step



OVER-SIZED FEET & FOOT PADS

Stability while you work



#1 IN LADDERS™

6200 SERIES STEPLADDER

Available in 3', 4', 5', 6', 7', 8', 10' and 12' models



Customize your ladder top with multiple accessories

4 rivets attach top to each front rail



Full set of rear horizontals spaced one per foot



Heavy duty internal spreaders connected with solid rivets



Seven layer fiberglass construction




Wider stance for stability



Back-up plates reinforce all top connectors



All steps and two rear horizontals* are knee-braced



Double riveted, slip-resistant Traction-Tred® steps



Model 6206

* Number of rear horizontal braces varies by model

★★★★★ **300** lbs. **LOAD CAPACITY**
Combined Weight of User and Materials

Type IA Duty Rating
EXTRA HEAVY DUTY/PROFESSIONAL USE



#1 IN LADDERS™

T6200 SERIES TWIN STEPLADDER

Available in 3', 4', 5', 6', 8', 10' and 12' models



LOCKTOP™

4 rivets attach top to each front rail

Back-up plates reinforce all top connectors

Heavy duty internal spreaders connected with solid rivets

All steps are knee-braced

Double riveted, slip-resistant Traction-Tred® steps

Seven layer fiberglass construction

Wider stance for stability

EDGE 360™

Model T6206

★★★★★ **300** lbs. **LOAD CAPACITY PER SIDE**
Combined Weight of User and Materials

Type IA Duty Rating
EXTRA HEAVY DUTY/PROFESSIONAL USE



#1 IN LADDERS™

P6200 SERIES PLATFORM LADDER

Available in 2', 4', 6', 8' and 10' models



Safety guard rail encourages proper ladder use

Large platform provides secure and comfortable work area




Full set of rear horizontals spaced one per foot

Back-up plates reinforce all top connectors



All steps are knee-braced



Double riveted, slip-resistant Traction-Tred® steps



Seven layer fiberglass construction



Wider stance for stability



Model P6204

★★★★★ **300** lbs. **LOAD CAPACITY**
Combined Weight of User and Materials

Type IA Duty Rating
EXTRA HEAVY DUTY/PROFESSIONAL USE



#1 IN LADDERS™

FTP SERIES TRIPOD STEPLADDER

Available in 4', 6', 8', 10' and 12' models



Convenient spreader handle design improves setup and transportability



Seven layer fiberglass construction

Molded external rail shield helps protect against abrasion and rail damage


Back-up plates reinforce all top connectors



Double riveted, slip-resistant Traction-Tred® steps



Wider stance for stability



Fully braced front section

Replaceable riveted, slip-resistant foot pad

Model FTP06

★★★★★ **300** lbs. **LOAD CAPACITY**
Combined Weight of User and Materials


Type IA Duty Rating
EXTRA HEAVY DUTY/PROFESSIONAL USE



#1 IN LADDERS™

6200 SERIES STEP STOOLS

Available in 2' and 3' models



6202 MODEL STEP STOOL



T6202 MODEL STEP STOOL



TW6200 SERIES PORTABLE WORK STAND

★★★★★ **300** lbs. **LOAD CAPACITY**
Combined Weight of User and Materials

Type IA Duty Rating
EXTRA HEAVY DUTY/PROFESSIONAL USE

Customize Your Ladder Top with Lock-In Accessories.



AC58-TL ToolLasso®



- Secures tools from falling
- Wraps around the grip of power tools, hand tools and caulk guns
- Locks into LOCKTOP™ to keep tools safe and ready to use
- Compatible with the ToolLasso® belt clip
- AC58-TL includes 1 belt clip and 2 ToolLassos

AC27-P Paint Cup



- Great for trim painting and cut-in applications
- Built-in magnet to secure a paint brush
- Holds 1 quart of paint
- Can be used with disposable Paint Cup Liner AC27-L

AC27-L Paint Cup Liner



- Disposable liner makes clean up easy
- Each AC-27L unit includes 4 liners

AC52-UB Utility Bucket



- Expand your work surface
- Great for jobsite or household use
- Integrated Lock-In Socket for adding Paint Cup, ToolLasso® or Utility Hook
- Ideal for wet or dry applications
- Holds up to one gallon of liquid, 25 lbs. capacity

AC56-UH Utility Hook



- Keep cords from getting tangled in your ladder
- Organize cords and keep them within reach
- Holds extension cords, air hoses, garden hoses, strands of lights, paint sprayers and other tools or project materials

AC50-JB-3 Job Bucket



- Increase ladder storage and maximize your work space
- Great for all trades: electrical, maintenance, plumbing, construction
- Integrated tape measure and screwdriver holders
- Top grooves hold round pipes in place
- 600 cubic inches of storage, 25 lbs. load capacity

AC54-JC Job Caddy



- Holds large or odd shaped items like fluorescent bulbs or ceiling fan blades
- 4 storage compartments keep small parts separated
- Screwdriver, pliers, putty knife & towel holders
- End hook built in for increased convenience
- Integrated Lock-In Socket for adding Paint Cup, ToolLasso® or Utility Hook



#1 IN LADDERS™

6200SERIES STEPLADDER

Model No.	Size	Approx. Width	Approx. Spread	Approx. Cu. Ft. Per Unit	Approx. Shipping Wt. Lbs.
6203	3'	18-1/8"	23-1/8"	2.0	13.0
6204	4'	19-7/8"	29"	3.0	16.0
6205	5'	21-5/8"	35-1/8"	4.1	19.0
6206	6'	23-3/8"	41-1/4"	5.3	22.0
6207	7'	25-1/8"	47-1/2"	6.6	26.0
6208	8'	26-7/8"	53-5/8"	8.1	30.0
6210	10'	30-3/8"	65-7/8"	12.5	39.0
6212	12'	33-7/8"	78-1/4"	15.0	48.0

Top: 5-3/4" x 13"
 Front Rails: 3-1/8" wide
 Front Flange: 1-3/16" wide
 Steps: 3" wide
 Rear Rails: 1-7/8" wide
 Rear Flange: 1-3/16" wide

T6200SERIES TWIN STEPLADDER

Model No.	Size	Approx. Width	Approx. Spread	Approx. Cu. Ft. Per Unit	Approx. Shipping Wt. Lbs.
T6203	3'	18-1/8"	29"	3.1	16.0
T6204	4'	19-7/8"	36-1/8"	4.6	19.0
T6205	5'	21-5/8"	43-1/8"	6.2	23.0
T6206	6'	23-3/8"	50-1/8"	8.0	27.0
T6208	8'	26-7/8"	64-1/8"	12.3	37.0
T6210	10'	30-3/8"	78-1/8"	17.3	54.5
T6212	12'	33-7/8"	92-1/8"	23.2	68.5

Top: 8-1/2" x 13"
 Front Rails: 3-1/8" wide
 Steps: 3" wide
 Flange: 1-3/16" wide

P6200SERIES PLATFORM LADDER

Model No.	Height (Size) to Platform	Rail Length	Approx. Width	Approx. Spread	Approx. Cu. Ft. Per Unit	Approx. Shipping Wt. Lbs.
P6202	2'	4'	23-3/8"	29-3/4"	4.2	17.0
P6204	4'	6'	26-7/8"	42"	7.2	24.0
P6206	6'	8'	30-3/8"	54-3/4"	10.9	32.0
P6208	8'	10'	33-7/8"	66-5/8"	15.2	44.5
P6210	10'	12'	37-3/8"	79"	20.1	55.0

Platform: 14-5/8" x 15"
 Front Rails: 3-1/8" wide
 Front Flange: 1-3/16" wide
 Steps: 3" wide
 Rear Rails: 1-7/8" wide
 Rear Flange: 1-3/16" wide

FTPSERIES TRIPOD STEPLADDER

Model No.	Size	Approx. Width	Approx. Spread	Approx. Cu. Ft. Per Unit	Approx. Shipping Wt. Lbs.
FTP6204	4'	31"	30-1/2"	3.7	17.0
FTP6206	6'	36"	43-3/4"	6.8	23.0
FTP6208	8'	40"	57"	10.1	31.0
FTP6210	10'	51"	71"	17.6	42.0
FTP6212	12'	54"	77-3/4"	22.6	51.0

Top: 5-3/4" x 13"
 Front Rails: 3-1/8" wide
 Flange: 1-3/16" wide
 Steps: 3" wide
 Rear Rail: 1-1/2" square (4' to 8')
 2" square (10' and 12')

6202MODEL STEP STOOL

Model No.	Size	Approx. Width	Approx. Spread	Approx. Cu. Ft. Per Unit	Approx. Shipping Wt. Lbs.
6202	2'	17-1/4"	19-1/2"	1.4	9.0

Top: 5-5/8" x 12-3/8"
 Front Rails: 3-1/8" wide
 Front Flange: 1-3/16" wide
 Steps: 3" wide
 Rear Rails: 1-3/4" wide
 Rear Flange: 1-3/16" wide
 5/8" wide front

T6202MODEL TWIN STEP STOOL

Model No.	Size	Approx. Width	Approx. Spread	Approx. Cu. Ft. Per Unit	Approx. Shipping Wt. Lbs.
T6202	2'	21-1/8"	23"	2.1	11.5

Steps: 3" wide Rails: 3-1/8" wide Flange: 1-3/16" wide

TW6200SERIES PORTABLE WORK STAND

Model No.	Size	Approx. Width	Approx. Spread	Approx. Cu. Ft. Per Unit	Approx. Shipping Wt. Lbs.
TW6202	2'	31-1/4"	22-1/4"	3.0	17.0
TW6203	3'	32-3/4"	29-3/4"	4.7	24.0

Top: 8" x 28" Front Rails: 3-1/4" wide Front Flange: 1-3/16" wide Steps: 3" wide



Werner Co. 93 Werner Rd. Greenville, PA 16125-9499
Phone: 888-523-3371 Fax: 888-456-8458 www.wernerco.com