



TPI 36M831 (306C) FIELD CALIBRATION

Step-by-Step Procedures

1. Fill a plastic or metal container with crushed ice and add clean water to a depth of at least 4 inches. Stir the ice and water for 2 to 3 minutes prior to performing calibration to ensure the water is completely chilled. Make certain there is plenty of ice in the mixture and always use clean water. Distilled water works well. The temperature of an ice bath is approximately 32°F (0°C).
2. Insert the stainless steel shaft of the 36M831 (306C) into the ice bath making sure at least one inch of the tip is immersed. Allow the reading on the thermometer to stabilize.
Note: The temperature reading must be within 23°F to 41°F (-5°C to 5°C for 36M831 (306C)) for calibration to have effect.
3. Press and hold the **ON/DH** button for approximately 8 seconds until “CAL” is displayed. “CAL” will display for approximately 2 seconds and then the 36M831 (306C) will return to normal operation. Calibration is complete.

Note: If the temperature reading was not within 23°F to 41°F (-5°C to 5°C for 306C) when step 3 was performed no change in calibration occurred. The 36M831 (306C) were designed with this feature to prevent improper calibration.