



#### NOTES:

1. TYPE: Swing
2. TURNS: Right
3. SWING ANGLE: 90 deg.
4. ITEM: Hydraulic Cylinder
5. FUNCTION: Double Acting
6. CLAMPING FORCE: 2600 lb.
7. BODY STYLE: Lower Flange
8. MAX. OIL FLOW: 100 cu. in./min.
9. PRESSURE RANGE: 500 to 5000 psi
10. MATERIAL OF CONSTRUCTION: Steel

COMPONENT	Swing Cylinders		
5UWU8	Swing Cylinder, Lower Flange, 2600 lb		UNIT
			INCH
			SHEET
			1 of 1

**GRAINGER**

100 Grainger Parkway, Lake Forest, Illinois 60045-5201  
 1-(800) GRAINGER, 1-(800) 472-4643, (847) 535-1000  
[www.grainger.com](http://www.grainger.com)

This file and any associated information and specifications are provided for reference and evaluation purposes only, and is subject to change without notice. Grainger makes no representations, warranties or guarantees as to the appropriateness, accuracy, completeness, or suitability for any purpose, of the file, information or specifications. You are solely responsible for the use of the file, information or specifications.

This drawing is the property of GRAINGER. It contains confidential, proprietary information that is GRAINGER property. Do not disclose to or duplicate for others except as authorized by GRAINGER.

SCALE 0.49